



Presets & Options:

- Vertical or horizontal drain
- Sleeve ground-shortly or wall-shortly
- Cold water, warm water, drain and electrical supply 230V must be presetted according to the regional directives
- Microsection direction:
Cupboards: side-walls, back-walls and doors vertical;
 Ground, cap, socket, shelves and light-bar horizontal;
Work-plate: horizontal in position of installation;
NAB: vertical front, horizontal socket
Faceplate: vertical front ; horizontal socket
- **ATTENTION:** Please, take note of the fire detector!

		Discher Technik GmbH Fuhr 4-6, 42781 Haan-Gruiten Tel.: +49 (0)2104/2336-0 Fax: +49 (0)2104/233699 E-mail: info@discher.de	Type of machine Compact_500-DT	
Customer No.:			Surface: Microsection	- polished with 240 grain size - finished with 280 grain size
Projekt-No.:	Status A			
Room		Material: 1.4301		
Date 04.12.2017	Drawn by: Trawert	Scale: 1:20	Measurements in mm	
File name: 18143-Compact_500-DT_GB		 DISCHER		
Duplication or transfer to third parties, even in extracts, requires the written permission of the Discher Company GmbH. State of the art and subject to change without prior notice.				